

BOARD WITH HOOKS MAX10 – LIGATURE RESISTANT



Colour: White with black edges. Delivered as standard with white hooks. Other colours (grey, black, beige and magenta) are available as options.

Also available as: Board w hooks Max10, 2 hooks (310x90x60 mm), Board w hooks Max10, 3 hooks (520x90x60 mm), Board w hooks Max10, 4 hooks (730x90x60 mm), Board w hooks Max10, 5 hooks (930x90x60 mm)

The ligature resistant Board with hooks Max10 is designed to minimise the risk of self-harm in environments with elevated safety requirements. The hook can hold the weight of several garments or damp towels without compromising function or safety.

- The Hook Max10 automatically releases in any direction when subjected to a load exceeding 10 kg.
- Bends gently and returns to its original shape
- Non-institutional design available in multiple colours

The Board with hooks Max10 are particularly suitable for all environments with high safety requirements, such as psychiatric care, youth care, treatment centres and correctional facilities. The Hook Max10 is the result of long-term and carefully considered product development. It is made from a unique, flexible material that causes the hook to bend under load and release at 10 kg or more – regardless of direction. This means that cords, straps or similar objects detach from the hook when subjected to force, thereby reducing the risk of use in self-harming through suspension. When the load is removed, the hook returns to its original shape and function, entirely without damage. The soft and compliant construction also reduces the risk of bodily injury in the event of a fall or accidental impact. Thanks to its discreet, everyday appearance, the hook does not appear institutional. The hook is available in five colour options – white, black, grey, beige and magenta – to suit a variety of rooms and interiors. The hook supports the weight of one or two garments or a heavier item such as a wet bath towel, but releases when additional force is applied. It does not break but bends, allowing the ligature to slip off. Release occurs in all directions, which means the hook can also be placed near doors or other sensitive areas. Design: Healsafe Interiör Suitable for installation in bathrooms, patient rooms or communal areas.

PRODUCT DATA

Material

Hook made of PC/ABS (core) and TPU (outer layer). The board is made of water resistant compact laminate.

Maintenance

The hook and board can be cleaned using a soft cloth and mild liquid detergent. If necessary, it may be disinfected using alcohol-based disinfectants. Do not use abrasive chemicals or scouring pads.

Technical data

HSI189 – Board with 2 hooks Max10 Size: B 310mm, W 90 mm, D 60 mm HSI190 - Board with 3 hooks Max10 Size: B 520 mm, W 90 mm, D 60 mm HSI191 - Board with 2 hooks Max10 Size: B 730 mm, W 90 mm, D 60 mm HSI192 - Board with 2 hooks Max10 Size: B 930 mm, W 90 mm, D 60 mm

Sustainability

Tests with string (Ø 1 mm), shoelace (8 x 1 mm) and rope made from bed sheets show that the hook releases the object at a load of up to 10 kg. The design and material of the hook are selected to extend the product's service life. The hook is sorted as hard plastic. The board is sorted as wood.

Delivery

1 week. Please note that unforeseen events may affect delivery. For current delivery times at the time of order confirmation or prior to placing an order, please contact us at info@healsafeinterior.com. For claims or complaints, please contact us at info@healsafeinterior.com.

Warranty

5 years. Applies under normal use. Full warranty provided against manufacturing defects.

Manufacturing/Production

Sweden.

Installation

The board must be mounted on a completely flat surface to ensure a tight and stable fit between the board and the wall. This minimises the space behind the board and makes it more difficult to attach cords, straps or similar items that could be used for self-harming purposes. Install using security screws. Installation must be carried out in accordance with the installation instructions